

Product data sheet

Specifications

Mureva Tube GT HF - GT bend - diam. 16 - black - IP40



IMT35206

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	Mureva
Product Or Component Type	Bend
Function Available	GT-function
Mounting Location	Indoor Outdoor
Nominal Cross Section	109 mm²
Diameter	External: 16 mm Internal: 11.8 mm
Colour Tint	Black (RAL 9005)

Complementary

Quantity Per Set	50 pieces
Ambient Air Temperature For Operation	-45...120 °C
Material	PC (polycarbonate)
Standards	IEC 61386 IEC 60754-2 EN 50267-2-2 EN 50267-2-1 NF F 16-102 IEC 60754-1 NF F 16-101

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK10
Environmental Characteristic	Non-flame propagating
Flame Retardance	M2
Level Or Class	F1
Product Certifications	NF CSTB

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.6 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	1.6 cm
Package 1 Length	29.5 cm
Package 1 Weight	33 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	25
Package 2 Height	12.5 cm
Package 2 Width	17 cm
Package 2 Length	29.5 cm
Package 2 Weight	840 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	200
Package 3 Height	30 cm
Package 3 Width	36 cm
Package 3 Length	50 cm
Package 3 Weight	7.186 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations