

Product data sheet

Specifications

Mureva Tube GT HF - GT bend - diam. 40 - black - IP40



IMT35210

⚠ Discontinued on: Dec 15, 2020

⚠ Discontinued

Main

Range Of Product	Mureva
Product Or Component Type	Bend
Function Available	GT-function
Mounting Location	Outdoor Indoor
Nominal Cross Section	940 mm²
Diameter	External: 40 mm Internal: 34.6 mm
Colour Tint	Black (RAL 9005)

Complementary

Quantity Per Set	25 pieces
Ambient Air Temperature For Operation	-45...120 °C
Material	PC (polycarbonate)
Standards	NF F 16-102 NF F 16-101 EN 50267-2-2 IEC 60754-2 IEC 61386 IEC 60754-1 EN 50267-2-1

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK10
Environmental Characteristic	Non-flame propagating
Flame Retardance	M2
Level Or Class	F1
Product Certifications	NF CSTB

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	20 cm
Package 1 Length	48 cm
Package 1 Weight	212 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations