



### Main

Range of product	Mureva Tube GT HF
Product or component type	Conduit sleeve
Mounting location	Indoor Outdoor
Diameter	External : 20 mm
Colour tint	Black (RAL 9005)

### Complementary

Material	PC (polycarbonate)
Quantity per set	50 pieces
Ambient air temperature for operation	-45...120 °C
Standards	IEC 60754-1 IEC 60754-2 EN 50267-2-1 EN 50267-2-2 IEC 61386


### Environment

IP degree of protection	IP41
IK degree of protection	IK10
Product certifications	NF
Environmental characteristic	Non-flame propagating
Environmental health and issues	Halogen free

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1839 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available  Product Environmental Profile
Product end of life instructions	Need no specific recycling operations
<b>Contractual warranty</b>	
Warranty period	18 months