

Product data sheet

Characteristics

IMT35336

Mureva – IP65 junc box – 14 membranes - 87x87 mm – w/o terminal - anthracite



Main

| | |
|---------------------------|-----------------------|
| Range of product | Mureva |
| Product or component type | Junction box |
| Device application | Cable installation |
| Colour tint | Anthracite (RAL 7016) |
| Quantity per set | Set of 5 |

Complementary

| | |
|--------------------|--------------------------|
| Device mounting | Surface |
| Fixing mode | By screws : body housing |
| Base dimension | 87 x 87 x 42 mm |
| Cable entry | Grommets |
| Cable entry number | 14 x 19 mm |
| Material | PP (polypropylene) |
| Terminals | Without terminal |
| Height | 87 mm |
| Width | 87 mm |
| Depth | 42 mm |
| Product weight | 62 g |

Environment

| | |
|---------------------------------------|----------------------------------|
| Ambient air temperature for operation | -25...60 °C |
| IP degree of protection | IP65 |
| Glow wire temp | 650 °C |
| Standards | EN 60670 |
| Product certifications | FIMKO SEMKO NEMKO DEMKO |
| Environmental characteristic | Halogen free |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications