

Product data sheet

Specifications



wall box, Multifix, 2 gangs box
67x40, polar white

IMT35924

Main

Range	Multifix
Product Or Component Type	Wall box
Device Presentation	Without cover

Complementary

Number Of Gangs	2 gangs
Fixing Mode	By screws and claws
Colour Tint	Polar white
Cable Entry	6 knock-out diameter: 20 mm 2 knock-out diameter: 16 mm
Height	67 mm
Width	134 mm
Depth	40 mm
Diameter	67 mm

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.100 cm
Package 1 Width	7.400 cm
Package 1 Length	14.200 cm
Package 1 Weight	57.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	12.000 cm
Package 2 Width	20.500 cm
Package 2 Length	33.500 cm
Package 2 Weight	694.000 g
Unit Type Of Package 3	S04

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	50
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	4.224 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations