



Main

Range of product	Multifix
Product name	Multifix Eco
Product or component type	Apparatus box
Device application	Double board
Quantity per set	Set of 25

Complementary

Device mounting	Flush
Device composition	Adjustable threaded screw ring Cover Stub with locking tabs of stainless steel
Mounting support	24...39 mm board
Number of combi-stubs	6 rigid Ø 16 mm / 20 mm combi-stub(s)
Number of gangs	1 gang
Colour tint	Grey NCS 3500
Material	PEHD (polyethylene high density) untreated
Distance between supports	60 mm
Diameter	71 mm
Internal depth	69 mm
Length	136 mm
Width	71 mm
Depth	104 mm
Product weight	0.113 kg
Cable cross section	2.5 mm ²
Tube diameter	20 mm
Sealing	Without
Connections - terminals	Snap-on

Environment

Standards	IEC 60670-1
Ambient air temperature for operation	-25...90 °C
IP degree of protection	IP20
Environmental characteristic	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------