

Product data sheet

Specifications



Mureva TED-DAV14 - strain relief - 23 mm

IMT36080

Main

Range Of Product	Mureva
Aesthetic Name	Mureva TED
Device Short Name	TED-DAV14
Product Or Component Type	Strain relief
Colour Tint	White
Quantity Per Set	5 pieces

Complementary

Product Destination	For up to Ø 14 mm cable
Material	PA (polyamide)
Length	23 mm
Width	60 mm
Depth	31.5 mm
Net Weight	0.0074 kg

Environment

Ambient Air Temperature For Operation	-25...40 °C
---------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.300 cm
Package 1 Width	3.100 cm
Package 1 Length	6.100 cm
Package 1 Weight	6.000 g
Unit Type Of Package 2	P06
Number Of Units In Package 2	3000
Package 2 Height	60.000 cm
Package 2 Width	80.000 cm
Package 2 Length	105.000 cm
Package 2 Weight	39492.000 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✓ Sustainable Packaging

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations