



Main

Range of product	Mureva
Product or component type	Junction box
Colour tint	White (RAL 9010)
Quantity per set	Set of 5

Complementary

Device mounting	Surface
Fixing mode	By screws : cover
Base dimension	87 x 87 x 39 mm
Cable entry	Grommets
Cable entry number	10 x 19 mm
Material	SEBS (styrene ethylene butylene styrene) : grommet PC (polycarbonate) : body and cover
Terminals	Screw terminals
Height	87 mm
Width	87 mm
Depth	39 mm
Product weight	0.089 kg

Environment

Ambient air temperature for operation	-25...40 °C
IP degree of protection	IP65
Glow wire temp	960 °C
Standards	CE UL 94 V0 EN 60670
Environmental characteristic	Halogen free Fire resistance

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

IMT36127 is replaced by:



IP55-65 Mureva U56 IMT34127

Mureva U56 - j box - 10 grommets fire resist - 5-pole screw term - polarwhite

Qty 1

Reason for Substitution: End of life | Substitution date: 01 July 2016