



Main

Range of product	Mureva
Aesthetic name	Mureva U56
Product or component type	Grommet
Colour tint	White (RAL 9010)
Quantity per set	10 pieces

Complementary

Material	SBS (styrene butadiene styrene)
Cable outer diameter	0...16 mm
Drilling diameter	19 mm
Product weight	0.0015 kg

Environment

Ambient air temperature for operation	-25...40 °C
IP degree of protection	IP65

Contractual warranty

Warranty period	18 months
-----------------	-----------

IMT36129 is replaced by:



IP55-65 Mureva U56 IMT34129

Mureva U56 - grommet white - diameter up to 16 mm UL - polarwhite

Qty 1

Reason for Substitution: End of life | Substitution date: 01 July 2016