



### Main

Range of product	Multifix
Product name	Multifix Prefal
Product or component type	Apparatus box
Quantity per set	Set of 25

### Complementary

Device mounting	Cast-in
Device composition	Adjustable threaded screw ring Cover Stub with locking tabs of stainless steel
Number of combi-stubs	4 flexible Ø 16 mm / 20 mm combi-stub(s)
Number of gangs	1 gang
Colour tint	Grey NCS 3500
Material	PEHD (polyethylene high density)
Distance between supports	60 mm
Internal depth	55 mm
Length	172 mm
Width	78 mm
Depth	71 mm
Product weight	0.105 kg
Cable cross section	2.5 mm <sup>2</sup>
Tube diameter	20 mm
Sealing	With

### Environment

Standards	IEC 60670-1
Ambient air temperature for operation	-25...60 °C

IP degree of protection	IP20
Environmental characteristic	Halogen free

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1839 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------