



Main

Range of product	Multifix
Product name	Multifix Prefal
Product or component type	Apparatus box
Device application	Single board
Quantity per set	Set of 25

Complementary

Device mounting	Flush
Device composition	Adjustable threaded screw ring Cover Stub with locking tabs of stainless steel
Mounting support	10...27 mm board
Number of combi-stubs	4 flexible Ø 16 mm / 20 mm combi-stub(s)
Number of cross stubs	2 Ø 16 mm / 20 mm cross stub(s)
Number of gangs	1 gang
Colour tint	Grey NCS 3500
Material	PEHD (polyethylene high density) untreated
Distance between supports	60 mm
Diameter	70 mm
Internal depth	55 mm
Length	172 mm
Width	114 mm
Depth	57 mm
Product weight	0.114 kg
Cable cross section	2.5 mm ²
Tube diameter	20 mm
Sealing	Without
Connections - terminals	Snap-on

Environment

Standards	IEC 60670-1
-----------	-------------

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP20
Environmental characteristic	Halogen free

Contractual warranty

Warranty period	18 months
-----------------	-----------