

Product data sheet

Specifications



Thorsman TET - grommet - grey - ISO M12 - diameter 3 to 5

IMT36179

Main

Product Range	Thorsman TET
Product Type	Grommet
Colour	Grey
Quantity Per Package	Set of 50

Complementary

Material	EPDM
Iso Thread	M12
Cable Outer Diameter	3...5 mm
Drilling Diameter	12.5 mm
Height	18 mm
Width	21 mm
Length	21 mm

Environment

Ip-Class	IP67
----------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.2 cm
Package 1 Width	2 cm
Package 1 Length	1.9 cm
Package 1 Weight	0.9 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	3.9 cm
Package 2 Width	14.5 cm
Package 2 Length	16.7 cm
Package 2 Weight	152 g
Unit Type Of Package 3	P12
Number Of Units In Package 3	3000

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Height	46 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	9 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)