

Product data sheet

Specifications



Thorsman TET - grommet - grey - ISO M50 - diameter 26 to 35

IMT36185

Main

Product Range	Thorsman TET
Product Type	Grommet
Colour	Grey
Quantity Per Package	Set of 25

Complementary

Material	EPDM
Iso Thread	M50
Cable Outer Diameter	26...35 mm
Drilling Diameter	50.7 mm
Height	13 mm
Width	20 mm
Length	20 mm

Environment

Ip-Class	IP67
----------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	6.0 cm
Package 1 Length	6.0 cm
Package 1 Weight	43.9 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	25
Package 2 Height	9.0 cm
Package 2 Width	15.0 cm
Package 2 Length	28.0 cm
Package 2 Weight	1.1 kg

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations