

# Product data sheet

Specifications



## Multifix Eco - apparatus box w/o cover - single - 4 flex combi stubs - 24/39mm

IMT36200

 **Discontinued on:** Dec 30, 2021

 **Discontinued**

### Main

Range Of Product	Multifix
Product Name	Multifix Eco
Device Short Name	VP-2 A
Product Or Component Type	Apparatus box
Device Application	Double board
Quantity Per Set	Set of 25

### Complementary

Device Mounting	Flush
Device Composition	Adjustable threaded screw ring Stub with locking tabs of stainless steel Without cover
Mounting Support	Board - thickness: 24...39 mm
Number Of Combi-StubS	4 flexible / 20 mm
Number Of Gangs	1 gang
Colour Tint	Grey (NCS 3500)
Material	PEHD (polyethylene high density) (untreated)
Distance Between Supports	60 mm
Diameter	70 mm
Internal Depth	55 mm
Length	170 mm
Width	69 mm
Depth	84 mm
Net Weight	0.096 kg
Cable Cross Section	2.5 mm <sup>2</sup>
Tube Diameter	20 mm
Sealing	Without
Connections - Terminals	Snap-on

### Environment

Standards	IEC 60670-1
-----------	-------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-25...90 °C
Ip Degree Of Protection	IP20

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	7.1 cm
Package 1 Length	16.7 cm
Package 1 Weight	82 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations