



Main

Range of product	Multifix
Product name	Multifix TED
Device short name	TED-A13 IG
Product or component type	Apparatus box
Device application	Single board
Quantity per set	Set of 100

Complementary

Device mounting	Flush
Device composition	Cast-in cover With stubs located 13 mm from the front edge of the box
Mounting support	Board
Number of stubs	3 Ø 16 mm stub(s)
Number of gangs	1 gang
Colour tint	Green
Material	PEHD (polyethylene high density) untreated
Distance between supports	60 mm
Diameter	74 mm
Internal depth	46 mm
Length	120 mm
Width	50 mm
Depth	48 mm
Cable cross section	2.5 mm ²
Tube diameter	16 mm
Sealing	With
Connections - terminals	Snap-on

Environment

Standards	IEC 60670-1
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP20
Environmental characteristic	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1839 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------