



### Main

Range of product	Multifix
Range	Multifix
Product name	Multifix Ceiling
Device short name	TB50/SH26
Product or component type	Ceiling box with stubs and knock-outs
Quantity per set	Set of 50

### Complementary

Device composition	Cover With stubs located 26 mm from the front edge of the box
Number of stubs	2 Ø 20 mm stub(s) 8 Ø 16 mm stub(s)
Cable entry	2 knock-out for 16 mm bottom conduit 2 knock-out for 20 mm bottom conduit
Colour tint	Grey
Material	PEHD (polyethylene high density) untreated
Diameter	83 mm
Distance between centers	70 mm
Length	145 mm
Width	145 mm
Depth	52 mm
Connections - terminals	Screw terminals
Sealing	Without
Internal depth	49 mm

### Environment

IP degree of protection	IP20
Environmental characteristic	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1001 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------