



## Main

Range of product	Mureva
Product or component type	Junction box
Colour tint	White (RAL 9010)
Quantity per set	Set of 5

## Complementary

Device mounting	Surface
Fixing mode	By screws : cover
Base dimension	87 x 87 x 39 mm
Cable entry	Grommets
Cable entry number	10 x 19 mm
Material	ABS (acrylonitrile butadiene-styrene) : body and cover SEBS (styrene ethylene butylene styrene) : grommet
Terminals	Without terminal
Height	87 mm
Width	87 mm
Depth	39 mm
Product weight	0.073 kg

## Environment

Ambient air temperature for operation	-25...40 °C
IP degree of protection	IP65
Glow wire temp	650 °C
Standards	CE EN 60670
Environmental characteristic	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## IMT36349 is replaced by:



### IP55-65 Mureva U56 IMT34349

Mureva U56 - j box - 10 grommets - without terminal - russian label - polarwhite

Qty 1

Reason for Substitution: End of life | Substitution date: 01 July 2016