



Main

Range of product	Mureva
Product or component type	Junction box
Colour tint	White (RAL 9010)
Quantity per set	Set of 5

Complementary

Device mounting	Surface
Fixing mode	By screws : cover
Base dimension	60 x 60 x 30 mm
Cable entry	Smooth faces
Material	Polyproben : body and cover
Terminals	Screw terminals
Height	60 mm
Width	60 mm
Depth	30 mm
Product weight	0.043 kg

Environment

Ambient air temperature for operation	-25...40 °C
IP degree of protection	IP20
Glow wire temp	650 °C
Standards	EN 60670
Product certifications	CE
Environmental characteristic	Halogen free

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

IMT36352 is replaced by:



IP20 Mureva K60 and TED IMT34352

Mureva K60 - j box w/o grommets - 5-p screw term - russian label - polarwhite

Qty 1

Reason for Substitution: End of life | Substitution date: 25 January 2017
