

Product data sheet

Characteristics

IMT37468

Mureva U56 - junction box - 10 grommets -
without terminal - DIY - 1 pack



Main

Range of product	Mureva
Product or component type	Junction box
Colour tint	White (RAL 9010)
Quantity per set	Set of 1

Complementary

Device mounting	Surface
Fixing mode	By screws : cover
Base dimension	87 x 87 x 39 mm
Cable entry	Grommets
Cable entry number	10 x 14 mm
Type of packing	Plastic bag and cardboard with eurohole
Material	ABS (acrylonitrile butadiene-styrene) : body and cover SEBS (styrene ethylene butylene styrene) : grommet
Terminals	Without terminal
Height	87 mm
Width	87 mm
Depth	39 mm

Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP65
Glow wire temp	650 °C
Standards	EN 60670
Product certifications	CE
Environmental characteristic	Halogen free

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

IMT37468 is replaced by:



IP55-65 Mureva U56 IMT34468

Mureva U56 - j box - 10 grommets - without terminal - DIY - 1 pack - polarwhite

Qty 1

Reason for Substitution: End of life | Substitution date: 01 July 2016
