



### Main

Range of product	Thorsman
Product or component type	Through bolt
Device short name	TEX
Provided equipment	Nut Washer
Quantity per set	Set of 100

### Complementary

Mounting support	Concrete Natural rock
Type of installation	Indoor
Thread type	M6
Screw length	70 mm
Drilling diameter	6 mm
Drilling depth	67 mm
Thickness	0...26 mm:[sapce]fixture
Embedding depth	35 mm
Tightening torque	8 N.m
Material	Steel electro-zinc
Atmospheric-corrosivity category	C2

### Environment

Ambient air temperature for operation	-20...60 °C
Product certifications	SITAC No. SC0268-10

### Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------