



Main

Range of product	Thorsman
Product or component type	Through bolt
Device short name	TEX
Provided equipment	Nut Washer
Quantity per set	Set of 100

Complementary

Mounting support	Concrete Natural rock
Type of installation	Indoor/outdoor
Thread type	M6
Screw length	70 mm
Drilling diameter	6 mm
Drilling depth	67 mm
Thickness	0...26 mm:[sapce]fixture
Embedding depth	35 mm
Tightening torque	8 N.m
Material	Steel hot-dip zinc
Atmospheric-corrosivity category	C3

Environment

Ambient air temperature for operation	-20...60 °C
Product certifications	SITAC No. SC0268-10

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------