



### Main

Range of product	Rapstrap
Product or component type	Releasable cable tie
Mounting mode	Clamped
Colour	Black

### Complementary

Maximum load	10 kg
Bundle size	< 5 mm > 80 mm
Material	Polyurethane elastomer
User manual language	Portuguese English French Spanish Dutch
Thickness	1.25 mm
Length	300 mm
Width	10 mm
Quantity per set	Set of 24
Type of packing	Plastic bag with eurohole

### Environment

Ambient air temperature for operation	-20...60 °C no-load -68 °C brittle point
Flame retardance	HB conforming to UL 94
Environmental characteristic	Limited resistance to prolonged UV exposure

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
China RoHS Regulation	<a href="#">China RoHS declaration</a>

---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

---