

Product data sheet

Specifications



Mureva Tube GT HF - GT conduit - diam. 16 - black - LSF0H - IP30

IMT49013

Main

Range Of Product	Mureva
Product Or Component Type	Rigid conduit
Shape	Tuliped ends
Function Available	GT-function
Mounting Location	Outdoor Indoor
Nominal Cross Section	95 mm²
Diameter	External: 16 mm Internal: 11 mm
Colour Tint	Black (RAL 9005)
Length	3 m

Complementary

Resistance To Compression	750 N
Material	PP (polypropylene)
Quantity Per Set	111 m
Ambient Air Temperature For Operation	-25...105 °C
Standards	IEC 60754-2 EN 50267-2-1 EN 50267-2-2 IEC 60754-1 IEC 61386

Environment

Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK07
Product Certifications	NF
Environmental Characteristic	Non-flame propagating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.6 cm
Package 1 Width	1.6 cm
Package 1 Length	300.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	72.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	111
Package 2 Height	14.0 cm
Package 2 Width	14.0 cm
Package 2 Length	301.0 cm
Package 2 Weight	8.0 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	2775
Package 3 Height	55.0 cm
Package 3 Width	301.0 cm
Package 3 Length	105.0 cm
Package 3 Weight	200.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations