

Product data sheet

Specifications



Mureva Tube GT HF - GT conduit - diam. 25 - black - LSF0H - IP30

IMT49015

Main

Range Of Product	Mureva
Product Or Component Type	Rigid conduit
Shape	Tuliped ends
Function Available	GT-function
Mounting Location	Indoor Outdoor
Nominal Cross Section	314 mm²
Diameter	External: 25 mm Internal: 20 mm
Colour Tint	Black (RAL 9005)
Length	3 m

Complementary

Resistance To Compression	750 N
Material	PP (polypropylene)
Quantity Per Set	57 m
Ambient Air Temperature For Operation	-25...105 °C
Standards	EN 50267-2-2 IEC 60754-1 EN 50267-2-1 IEC 61386 IEC 60754-2

Environment

Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK07
Product Certifications	NF
Environmental Characteristic	Non-flame propagating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13 cm
Package 1 Width	13 cm
Package 1 Length	300 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	154 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	57
Package 2 Height	10.5 cm
Package 2 Width	13 cm
Package 2 Length	301 cm
Package 2 Weight	8.8 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	2280
Package 3 Height	80 cm
Package 3 Width	301 cm
Package 3 Length	105 cm
Package 3 Weight	354 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations