

# Product data sheet

Specifications



## Mureva Tube GT HF - GT conduit - diam. 40 - black - LSF0H - IP30

IMT49017

### Main

|                           |                                    |
|---------------------------|------------------------------------|
| Range Of Product          | Mureva                             |
| Product Or Component Type | Rigid conduit                      |
| Shape                     | Tuliped ends                       |
| Function Available        | GT-function                        |
| Mounting Location         | Indoor<br>Outdoor                  |
| Nominal Cross Section     | 907 mm²                            |
| Diameter                  | External: 40 mm<br>Internal: 34 mm |
| Colour Tint               | Black (RAL 9005)                   |
| Length                    | 3 m                                |

### Complementary

|                                       |   |
|---------------------------------------|---|
| Resistance To Compression             | 750 N   |
| Material                              | PP (polypropylene)  |
| Quantity Per Set                      | 21 m  |
| Ambient Air Temperature For Operation | -25...105 °C  |
| Standards                             | EN 50267-2-2<br>IEC 60754-1<br>IEC 61386<br>IEC 60754-2<br>EN 50267-2-1 |

### Environment

|                              |                       |
|------------------------------|-----------------------|
| Ip Degree Of Protection      | IP30                  |
| Ik Degree Of Protection      | IK07                  |
| Product Certifications       | NF                    |
| Environmental Characteristic | Non-flame propagating |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 13.0 cm  |
| Package 1 Width              | 13.0 cm  |
| Package 1 Length             | 300.0 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |          |
|------------------------------|----------|
| Package 1 Weight             | 266.0 g  |
| Unit Type Of Package 2       | CAR      |
| Number Of Units In Package 2 | 21       |
| Package 2 Height             | 12.0 cm  |
| Package 2 Width              | 12.0 cm  |
| Package 2 Length             | 301.0 cm |
| Package 2 Weight             | 5.6 kg   |
| Unit Type Of Package 3       | PAL      |
| Number Of Units In Package 3 | 525      |
| Package 3 Height             | 50.0 cm  |
| Package 3 Width              | 301.0 cm |
| Package 3 Length             | 105.0 cm |
| Package 3 Weight             | 140.0 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |