



has not been replaced. Please contact your customer care center for more information.

Main

Range of product	Stago
Product or component type	Internal corner
Colour tint	Optional
Quantity per set	Set of 1

Complementary

Trunking dimension	170A x 65 mm
Compartment partitioning	1 compartment
Front opening size	80 mm
Nominal cross section	11050 mm ²
Fixing mode	By screws
Material	Zinc coated sheet steel
Surface finish	Powder coated
Length	115 mm
Height	170 mm
Width	65 mm

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient air temperature for operation	-20...60 °C
Environmental health and issues	Halogen free
IP degree of protection	IP20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.