


Product data sheet

Specifications



Stago - bend 90 kit, riser/dropper - 170 x 65 mm - steel - white - RAL9010

INS5553503

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range Of Product	Stago
Product Or Component Type	Bend
Provided Equipment	1 x cover
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 1

Complementary

Trunking Dimension	170 x 65 mm
Compartment Partitioning	1 compartment
Operating Angle	90 °
Direction Change Type	Vertical
Front Opening Size	80 mm
Nominal Cross Section	11050 mm²
Fixing Mode	By brackets By screws
Material	Zinc coated sheet steel
Surface Finish	Powder coated
Length	250 mm
Height	170 mm
Width	65 mm
Compatibility Code	WGX-LSU170

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient Air Temperature For Operation	-20...80 °C
Ip Degree Of Protection	IP20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17 cm
Package 1 Width	6.5 cm
Package 1 Length	25 cm
Package 1 Weight	1.12 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations