



Main

Range of product	Stago
Product or component type	Bend
Provided equipment	1 x cover
Colour tint	Optional
Quantity per set	Set of 1

Complementary

Trunking dimension	170A x 65 mm
Compartment partitioning	1 compartment
Operating angle	90 °
Direction change type	Vertical
Front opening size	80 mm
Nominal cross section	11050 mm ²
Fixing mode	By brackets By screws
Material	Zinc coated sheet steel
Surface finish	Powder coated
Length	250 mm
Height	170 mm
Width	65 mm

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient air temperature for operation	-20...60 °C
Environmental health and issues	Halogen free

