


Product data sheet

Specifications



Stago - branching piece upward - 170A x 65 mm - steel - white - RAL 1013

INS5553712

⚠ Discontinued on: Sep 26, 2017

⚠ End-of-service on: Oct 26, 2017

⚠ Discontinued

Main

Range Of Product	Stago
Product Or Component Type	Branching piece
Colour Tint	White (RAL 1013)
Quantity Per Set	Set of 1

Complementary

Trunking Dimension	170A x 65 mm
Compartment Partitioning	1 compartment
Nominal Cross Section	11050 mm ²
Front Opening Size	80 mm
Fixing Mode	By screws By brackets
Material	Zinc coated sheet steel
Length	300 mm
Height	170 mm
Width	65 mm

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17 cm
Package 1 Width	6.5 cm
Package 1 Length	40 cm
Package 1 Weight	1340 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

