



has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

Main

| | |
|---------------------------|-----------------|
| Range of product | Stago |
| Product or component type | Internal corner |
| Colour tint | Optional |
| Quantity per set | Set of 1 |

Complementary

| | |
|--------------------------|--------------------------|
| Trunking dimension | 165V x 52 mm |
| Compartment partitioning | 1 compartment |
| Front opening size | 80 mm |
| Nominal cross section | 8580 mm ² |
| Fixing mode | By brackets By screws |
| Material | Zinc coated sheet steel |
| Surface finish | Powder coated |
| Length | 200 mm |
| Height | 165 mm |
| Width | 52 mm |

Environment

| | |
|---------------------------------------|--------------------------------------|
| Standards | EN 50085-1:2005 EN 50085-2-1:2006 |
| Directives | 73/23/EEC - low voltage directive |
| Ambient air temperature for operation | -20...60 °C |
| Environmental health and issues | Halogen free |
| IP degree of protection | IP20 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications