

# Product data sheet

## Characteristics

# INS5554806

Stago - stop end right - 165V x 52 mm - steel - optional colour



has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

### Main

Range of product	Stago
Product or component type	Stop end
Colour tint	Optional
Quantity per set	Set of 1

### Complementary

Trunking dimension	165V x 52 mm
Compartment partitioning	1 compartment
Front opening size	80 mm
Nominal cross section	8580 mm <sup>2</sup>
Fixing mode	Snap-fitted
Material	Zinc coated sheet steel
Surface finish	Powder coated
Depth	11 mm
Height	165 mm
Width	52 mm

### Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient air temperature for operation	-20...60 °C
Environmental health and issues	Halogen free
IP degree of protection	IP20

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications