



Main

Range of product	Stago
Product or component type	Stop end
Colour tint	White (RAL 1013)
Quantity per set	Set of 1

Complementary

Trunking dimension	165V x 52 mm
Compartment partitioning	1 compartment
Front opening size	80 mm
Nominal cross section	8580 mm ²
Fixing mode	Snap-fitted
Material	Zinc coated sheet steel
Surface finish	Powder coated
Depth	11 mm
Height	165 mm
Width	52 mm
Compatibility code	WGX-ESH165V

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient air temperature for operation	-20...80 °C
Environmental health and issues	Halogen free
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------