

Product data sheet

Specifications



Stago - stop end - 165W x 52 mm - steel - optional colour

INS5554811

 **Discontinued on:** Jun 11, 2019

 **Discontinued**

Main

Range Of Product	Stago
Product Or Component Type	Stop end
Colour Tint	Optional
Quantity Per Set	Set of 1

Complementary

Trunking Dimension	165W x 52 mm
Compartment Partitioning	1 compartment
Front Opening Size	80 mm
Nominal Cross Section	8580 mm²
Fixing Mode	Snap-fitted
Material	Zinc coated sheet steel
Surface Finish	Powder coated
Depth	11 mm
Height	165 mm
Width	52 mm

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.5 cm
Package 1 Width	5.2 cm
Package 1 Length	1.1 cm
Package 1 Weight	75 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

