



Main

Range of product	Stago
Product or component type	Bend
Provided equipment	2 x cover
Colour tint	White (RAL 9010)
Quantity per set	Set of 1

Complementary

Trunking dimension	183 x 72 mm
Compartment partitioning	2 compartments
Operating angle	90 °
Direction change type	Vertical
Front opening size	40 mm 80 mm
Nominal cross section	13176 mm ²
Fixing mode	By screws By brackets
Material	Zinc coated sheet steel
Surface finish	Powder coated
Length	250 mm
Height	183 mm
Width	72 mm

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient air temperature for operation	-20...60 °C
Environmental health and issues	Halogen free
IP degree of protection	IP20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations