



has not been replaced. Please contact your customer care center for more information.

### Main

Range of product	Stago
Product or component type	T-piece
Provided equipment	2 x cover
Colour tint	White (RAL 1013)
Quantity per set	Set of 1

### Complementary

Trunking dimension	183 x 72 mm
Compartment partitioning	2 compartments
Front opening size	40 mm 80 mm
Nominal cross section	13176 mm <sup>2</sup>
Fixing mode	By brackets By screws
Material	Zinc coated sheet steel
Surface finish	Powder coated
Length	400 mm
Height	183 mm
Width	72 mm

### Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient air temperature for operation	-20...60 °C
Environmental health and issues	Halogen free
IP degree of protection	IP20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications