



### Main

Range of product	Stago
Product or component type	Stop end
Colour tint	White (RAL 9010)
Quantity per set	Set of 1

### Complementary

Trunking dimension	183 x 72 mm
Compartment partitioning	2 compartments
Front opening size	40 mm 80 mm
Nominal cross section	13176 mm <sup>2</sup>
Fixing mode	Snap-fitted
Material	Zinc coated sheet steel
Surface finish	Powder coated
Depth	11 mm
Height	183 mm
Width	72 mm

### Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Directives	73/23/EEC - low voltage directive
Ambient air temperature for operation	-20...60 °C
Environmental health and issues	Halogen free
IP degree of protection	IP20

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations