

Product data sheet

Specifications



Stago - t-piece, riser - 233-2 x 72 mm - steel - optional colour

INS5558601

⚠ Discontinued on: Jun 11, 2019

⚠ Discontinued

Main

| | |
|---------------------------|-----------|
| Range Of Product | Stago |
| Product Or Component Type | T-piece |
| Provided Equipment | 2 x cover |
| Colour Tint | Optional |
| Quantity Per Set | Set of 1 |

Complementary

| | |
|--------------------------|--------------------------|
| Trunking Dimension | 233 x 72 mm |
| Compartment Partitioning | 2 compartments |
| Front Opening Size | 80 mm |
| Nominal Cross Section | 16776 mm² |
| Fixing Mode | By screws By brackets |
| Material | Zinc coated sheet steel |
| Surface Finish | Powder coated |
| Length | 400 mm |
| Height | 233 mm |
| Width | 72 mm |

Environment

| | |
|---------------------------------------|--------------------------------------|
| Standards | EN 50085-1:2005 EN 50085-2-1:2006 |
| Directives | 73/23/EEC - low voltage directive |
| Ambient Air Temperature For Operation | -20...60 °C |
| Ip Degree Of Protection | IP20 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 23.3 cm |
| Package 1 Width | 7.2 cm |
| Package 1 Length | 40 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|--------|
| Package 1 Weight | 1848 g |
|------------------|--------|