



Main

Range of product	Thorsman
Product name	Thorsman CYB
Product or component type	Socket-outlet
Device presentation	Connection kit
Provided equipment	Wieland male/female push-in installation coupler
Colour tint	White RAL 1013
Quantity per set	Set of 1

Complementary

Device composition	Strain relief Protective cover End piece
[In] rated current	16 A
[Ue] rated operational voltage	250 V
Number of power socket outlets	3 side earth
Ground lug position	37° ground lug
Number of cables	2 x 1.1 m, 3 x 2.5 mm ² wire
Device connection	Combined with slave outlet
Fixing mode	Snap-fitted
Material	PC/ABS
Length	142 mm
Height	84 mm
Width	50 mm

Environment

Standards	IEC 60884-1
Ambient air temperature for operation	-20...40 °C
IP degree of protection	IP20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.