


Product data sheet

Specifications



OptiLine 50 - cable connector - GST 15i5 female

INS70000

 **Discontinued on:** Sep 30, 2022

 **Discontinued**

Main

Range Of Product	OptiLine 50
Product Type	Cable connector
Additional Information	Unassembled
Colour	White
Quantity Package 1 / Unit	10 pieces

Complementary

Interface	GST 15i5 female
Rating	16 A - 250/400 V
Product Material	PA (polyamide)
Connections - Terminals	Screw connection
Suitable For	0.5...2.5 mm², 7.8...13.5 mm, fine stranded 0.5...2.5 mm², 7.8...13.5 mm, rigid
Length	78 mm
Height	15 mm
Width	32 mm

Environment

Operating Temperature	-5...40 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.6 cm
Package 1 Width	3.3 cm
Package 1 Length	6.8 cm
Package 1 Weight	22 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	20 cm
Package 2 Length	30 cm
Package 2 Weight	265 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	150
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	5.374 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations