



Main

Range of product	OptiLine 50
Product type	Cable connector
Additional information	Unassembled
Colour	White
Quantity package 1 / unit	Set of 10

Complementary

Interface	GST 18i3 female (3 poles)
Rating	16 A - 250 V
Product material	PA (polyamide)
Connections - terminals	Screw connection
Suitable for	Fine stranded, cable cross section: 0.75...2.5 mm ² : Ø 6.5...10.5 mm Rigid, cable cross section: 0.75...2.5 mm ² : Ø 6.5...10.5 mm
Length	70 mm
Height	13 mm
Width	28 mm

Environment

Operating temperature	-5...40 °C
IP degree of protection	IP20

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1001 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------