

Product data sheet

Specifications



OptiLine 50 - extension cable - GST 15i5 female/male - H05Z1A7Z1-F - 1 m

INS74001

⚠ Discontinued on: Jun 30, 2022

⚠ Discontinued

Main

Range Of Product	OptiLine 50
Product Type	Extension cable
Colour	White
Quantity Package 1 / Unit	30 pieces

Complementary

Type Of Cable	H05Z1A7Z1-F
Interface	GST 15i5 female/male
Network Number Of Phases	3 phases
Rating	16 A - 250/400 V
Number Of Poles	5
Product Material	PA (polyamide)
Cable Cross Section	2.5 mm ²
Cable Outer Diameter	12.3 mm
Cable Length	1 m
Height	15 mm
Width	33 mm

Environment

Environmental Characteristic	Fire retardant
------------------------------	----------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	28.2 cm
Package 1 Length	37.7 cm
Package 1 Weight	261 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	No need of specific recycling operations
---------------------	--