

# Product data sheet

Specifications



## OptiLine 50 - feeding cable - GST 15i5 female/free end - S05Z1A7Z1-F3G1.5 - 10 m

INS74210

 **Discontinued on:** Jun 30, 2022

 **Discontinued**

### Main

Range Of Product	OptiLine 50
Product Type	Feeding cable
Colour	White
Quantity Package 1 / Unit	5 pieces

### Complementary

Type Of Cable	S05Z1A7Z1-F3G1.5
Interface	GST 15i5 female/free end
Network Number Of Phases	3 phases
Rating	16 A - 250 V
Number Of Poles	5
Product Material	PA (polyamide)
Cable Cross Section	2.5 mm <sup>2</sup>
Cable Outer Diameter	12.3 mm
Cable Length	10 m
Height	15 mm
Width	33 mm

### Environment

Operating Temperature	-5...40 °C
Environmental Characteristic	Fire retardant
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	28 cm
Package 1 Length	38 cm
Package 1 Weight	2.306 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---

Circularity Profile	No need of specific recycling operations
---------------------	--