

# Product data sheet

Specifications



## OptiLine 45 - installation trunking - 75x55 mm - PVC - polar white - 3000 mm

ISM10110P

### Main

Range Of Product	OptiLine 45
Cabling Installation System	Trunking
Product Or Component Type	Installation trunking
Colour Tint	Polar white (RAL 9003)
Quantity Per Set	24 m

### Complementary

Trunking Material	Plastic
Trunking Dimension	75 x 55 mm
Compartment Partitioning	1 compartment
Fixing Mode	By screws
Front Opening Size	45 mm
Material	PVC (polyvinyl chloride)
Length	3000 mm
Height	75 mm
Width	55 mm

### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002 NF C 68-102
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	3
Package 1 Height	5.5 cm
Package 1 Width	7.5 cm
Package 1 Length	300.0 cm
Package 1 Weight	2.63 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BB1
Number Of Units In Package 2	24
Package 2 Height	13.0 cm
Package 2 Width	25.0 cm
Package 2 Length	306.0 cm
Package 2 Weight	21.25 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	384
Package 3 Height	79.0 cm
Package 3 Width	120.0 cm
Package 3 Length	306.0 cm
Package 3 Weight	365.0 kg

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations