



❗ Discontinued

## Commercial status

Discontinued: 30 May 2017

End-of-service: 06 February 2018

## Main

Cabling installation system	Post Pole Trunking
Product or component type	Locking clip

## Complementary

Type of pole	Two-sided One-sided
Type of post	One-sided Two-sided
Colour tint	White (RAL 9010)
Quantity per set	Set of 10
Trunking material	Aluminium Plastic
Trunking dimension	75 x 55 mm 95 x 55 mm 165 x 55 mm 185 x 55 mm 140 x 55 mm
Pole/Post surface finish	Anodized Powder coated
Pole fixing mode	Tension-mounted Free-standing
Fixing mode	Snap-fitted
Material	PC/ABS
Length	23 mm
Height	45 mm
Width	23 mm
Market segment	Small commercial Residential

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30
IK degree of protection	IK07

## Contractual warranty

Warranty	18 months
----------	-----------

## ISM10906 is replaced by:



### Trunking ISM10906P

OptiLine 45 - locking clip - polar white

Qty 1

Reason for Substitution: End of life | Substitution date: 01 July 2014