



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Stop end
Colour	Aluminium metallic
Quantity package 1 / unit	Set of 2

Complementary

Trunking material	Aluminium
Trunking dimension	80 x 55 mm
Fixing mode	Screw Snap-fitted
Product material	PC/ABS painted
Length	21 mm
Height	64 mm
Width	56 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------