

Product data sheet

Specifications



OptiLine 70 - installation trunking - 185x55 mm - aluminium - natural - 2000 mm

ISM11550

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range Of Product	OptiLine 70
Cabling Installation System	Trunking
Product Or Component Type	Installation trunking
Colour Tint	Natural
Quantity Per Set	4 m
Market Segment	Residential Small commercial

Complementary

Trunking Material	Aluminium
Trunking Dimension	185 x 55 mm
Compartment Partitioning	2 compartments
Mounting Location	Internal
Fixing Mode	By screws
Front Opening Size	70 mm
Material	Aluminium anodized
Length	2000 mm
Height	185 mm
Width	55 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP40

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	2
Package 1 Height	195 cm
Package 1 Width	225 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	2000 cm
Package 1 Weight	12 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	4
Package 2 Height	19.5 cm
Package 2 Width	22.5 cm
Package 2 Length	206 cm
Package 2 Weight	24 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	60
Package 3 Height	72.5 cm
Package 3 Width	120 cm
Package 3 Length	205 cm
Package 3 Weight	375.76 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
--------------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
------------------------------	---

Environmental Disclosure	Product Environmental Profile
---------------------------------	---

Circularity Profile	No need of specific recycling operations
----------------------------	--