



Main

Range of product	Optiline
Cabling installation system	Trunking
Product type	Mini trunking
Trunking type	Mini trunking

Complementary

Trunking material	Plastic
Compartment partitioning	2 compartments
Colour	White (RAL 9003)
Trunking dimension	12 x 30 mm
Fixing mode	Pre-punched fixing hole 100 mm
Material	PVC (polyvinyl chloride)
Quantity per package	21 m
Operating temperature	-25...60 °C
Length	2100 mm
Height	30 mm
Width	12 mm

Environment

Standards	73/23/EEC EN 50085-1 : 2005 EN 50085-2-1 : 2006
IP degree of protection	IP40
IK degree of protection	IK07