

# Product data sheet

## Characteristics

# ISM14400

OptiLine - minitrunking - 18 x 35 mm - PVC - white



### Main

Range of product	Optiline
Cabling installation system	Trunking
Product type	Mini trunking
Trunking type	Mini trunking

### Complementary

Trunking material	Plastic
Compartment partitioning	2 compartments
Colour	White (RAL 9010)
Trunking dimension	18 x 35 mm
Fixing mode	Power cable : screw-fixed Pre-punched fixing hole 100 mm
Material	PVC (polyvinyl chloride)
Quantity per package	42 m
Operating temperature	-25...60 °C
Length	2100 mm
Height	35 mm
Width	18 mm

### Environment

Standards	73/23/EEC EN 50085-1 : 2005 EN 50085-2-1 : 2006
IP degree of protection	IP40
IK degree of protection	IK07

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1826 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---