

# Product data sheet

Specifications



## Stop end, OptiLine, for 18x35mm trunking, PC/ABS, polar white

ISM14404P

### Main

Range	OptiLine
Cabling Installation System	Mini trunking
Product Type	Stop end
Trunking Type	Mini trunking
D_Range_Compatibility	OptiLine

### Complementary

Trunking Material	Plastic
Colour Tint	Polar white (RAL 9003)
Trunking Dimension	18 x 35 mm
Fixing Mode	Snap-fitted
Material	PC/ABS
Quantity Per Package	Set of 10
Operating Temperature	-5...60 °C
Length	37 mm
Height	19 mm
Width	15 mm

### Environment

Standards	73/23/EEC EN 50085-1:2005 EN 50085-2-1:2006
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.700 cm
Package 1 Width	1.500 cm
Package 1 Length	1.900 cm
Package 1 Weight	2.000 g
Unit Type Of Package 2	BB1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	10
Package 2 Height	1.800 cm
Package 2 Width	10.000 cm
Package 2 Length	17.000 cm
Package 2 Weight	25.000 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	500
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1.636 kg

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   Transparency   RoHS/REACH

## Resource performance

✓ Sustainable Packaging

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations