

Product data sheet

Specifications



OptiLine - minitrunking - 18 x 45 mm - PVC - cable retain - polar white - FR

ISM14531P

 **Discontinued on:** Sep 30, 2022

 **Discontinued**

Main

Range Of Product	Optiline
Cabling Installation System	Trunking
Product Type	Mini trunking
Trunking Type	Mini trunking

Complementary

Trunking Material	Plastic
Compartment Partitioning	1 compartment
Colour	White (RAL 9003)
Trunking Dimension	18 x 45 mm
Fixing Mode	Pre-punched fixing hole 100 mm Power cable: screw-fixed
Material	PVC (polyvinyl chloride)
Quantity Per Package	42 m
Operating Temperature	-25...60 °C
Length	2100 mm
Height	45 mm
Width	18 mm

Environment

Standards	73/23/EEC EN 50085-1:2005 EN 50085-2-1:2006
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	4.5 cm
Package 1 Length	100 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	349.5 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	40
Package 2 Height	9.6 cm
Package 2 Width	21.5 cm
Package 2 Length	213 cm
Package 2 Weight	14.28 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	720
Package 3 Height	38.4 cm
Package 3 Width	120 cm
Package 3 Length	220 cm
Package 3 Weight	377 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations